




# High Linearity Position Sensing Detector

Part number: \$2 – 0425 Description: 2L30\_SU106

The SiTek 2L30 PSD functions according to the lateral effect photodiode principle. It is an analogue device and therefore displays excellent position resolution. The resolution is determined by the system signal-to-noise-ratio.

The 2L30 is operated in the biased mode. Typical applications include: distance and height measurements, position and motion measurements and vibration studies.

Special UV-or YAG-enhanced versions are available.



Electrical specificatio	n				
Parameter	Symbol	Min.	Тур.	Max.	Unit
Active area			30 x 30		$mm^2$
Position non-linearity			0,3	0,8	%
Detector resistance	$R_{det}$	7	10	16	kΩ
Leakage current	$I_d$		200	2000	nA
Noise current	$I_{\text{noise}}$		1,3	1,8	pA/√Hz
Responsivity	r		0,63		A/W
Capacitance	$C_{i}$		730	900	рF
Rise time (10% - 90%)	t <sub>r</sub>		3,3	6,4	μs
Bias voltage (reverse)	$V_R$	5	15	30	V
Thermal drift			40	200	ppm/°C

### Absolute maximum ratings

Parameter	Symbol	Value	Unit
Reverse voltage	$V_{R\text{-max}}$	30	V
Operating temperature	Toper	70	°C
Storage temperature	Tstg	100	°C

**Test conditions:** Room temperature 23 °C, bias voltage ± 15 V, light source wavelength

940 nm. Position non-linearity and thermal drift are valid within  $80\ \%$  of

the detector length.

**Package:** 8 pin DIP ceramic substrate, 48 x 44 mm<sup>2</sup>, with solderable pins and

protective window.


Germany & Other Countries Laser Components GmbH Tel: +49 8142 2864 - 0 Fax: +49 8142 2864 - 11 info@lasercomponents.com www.lasercomponents.com

France
Laser Components S.A.S.
Tel: +33 1 39 59 52 25
Fax: +33 1 39 59 53 50
info@lasercomponents.fr
www.lasercomponents.fr

United Kingdom

laser Components (UK) Ltd.
Tel: +44 1245 491 499
Fax: +44 1245 491 801
info@lasercomponents.co.uk
www.lasercomponents.co.uk






#### **Application Information**

The inherent resolution of a PSD is very good. It is proven to be better than one part in one million. The

0,6

performance of a PSD based measurement system is thus limited by its mechanical, optical electrical components. To get the best performance you have to consider:

- Modulated light source. Modulation makes it possible
- to avoid influence of other light sources.
- Stable temperature.
- · Mechanical stable system.
- High optical resolution.
- High resolution in division of sum- and difference signals Resolution, optical sensitivity and measurement speed are related to each other in the PSD measurement system and you have to make the proper choices and tradeoffs for your system.



## **SEEPOS - SiTek PSD Signal Processing System**

For most position measurement application the SiTek SEEPOS system offers a complete and easy-to use solution. It is a versatile PSD signal processing tool optimized for development of PSD systems. High speed PSD electronics combined with digital signal processing and high speed USB transfer makes it possible to build your own powerful measurement system.

Information in this data sheet is believed to be reliable. However, no responsibility is assumed for possible inaccuracies or omissions. Specifications

Date: 2019-12-04

Reg.No. S2-0425-D\_A

Germany & Other Countries Laser Components GmbH

Tel: +49 8142 2864 - 0 Fax: +49 8142 2864 - 11 info@lasercomponents.com www.lasercomponents.com

Laser Components S.A.S. Tel: +33 1 39 59 52 25 Fax: +33 1 39 59 53 50 info@lasercomponents.fr www.lasercomponents.fr

#### United Kingdom

Laser Components (UK) Ltd. Tel: +44 1245 491 499 Fax: +44 1245 491 801 info@lasercomponents.co.uk www.lasercomponents.co.uk