

Data Sheet

# VIAVI ORL-85

## SmartClass™ Fiber Inspection-Ready Optical Return Loss Meters

The SmartClass Fiber ORL-85 combines fiber inspection, optical power meter (OPM), light source (OLS), and continuous wave return loss meter (OCWR) in one versatile test instrument. The compact instrument is ideal for measuring optical return loss and inspecting fiber connector end faces to verify optical connection quality.

Optical systems with high-speed lasers, analog transmission (CATV), or Raman amplifiers require high return loss for maximum performance. Furthermore, optical return loss measurements can be used to prove that an installation was completed carefully and accurately; for example, they can show that the optical connectors were inspected and are clean. The ultra-sensitive power meter combined with stabilized light sources enable up to a 70 dB measurement range. The angled single-mode test port (APC) guarantees highly accurate return loss measurements without requiring external termination for up to 50 dB return loss measurements.



The ORL-85 is compatible with the P5000i digital analysis microscope for checking fiber end-face quality and getting pass/fail acceptance results at the push of a button.

Threshold settings for pass/fail indications and the intuitive touch screen user interface transforms users into instant fiber experts without the need for special training. Automatic functions, such as Auto- $\lambda$  and real-time Multi- $\lambda$  functionalities avoid handling errors and speed up test time significantly. The ORL-85 is fully compatible with other members of the SmartClass Fiber family (OLS, OLP, and OLT) with these automatic functions.

Users can easily save test results (power, return loss, and fiber inspection) with real-time stamp to generate certification reports. Test results can be easily uploaded to a PC for post-processing with FiberChekPRO™ PC software.

The ORL-85 optical return loss meters can be used anywhere today's fiber technicians go, up poles or down holes. Technicians gain ultimate flexibility and performance from this powerful easy-to-use solution that can instantly transform any technician into a fiber expert.

### Benefits

- Complete jobs faster, correctly, and on time—the first time—with a uniquely integrated fiber inspection microscope, optical power meter, optical light source, and optical return loss meter
- Battery-operated, field-portable instrument provides a full day of autonomy
- Data transfer and remote control via USB, Ethernet or optional WiFi connection
- Shielded housing for extreme accuracy in RF environments
- Rugged, weather-proof design for outdoor use

### Features

- Real-time simultaneous return loss measurements at multiple wavelengths
- Automated pass/fail fiber inspection analysis with optional P5000i microscope
- Onboard fiber inspection and test results storage with time stamp
- 70 dB high precision return loss meter
- 3.5" color touch screen with integrated stylus
- In-service loss test option

## Specifications

	ORL-85 (2311/21)	ORL-85 (2311/23)
<b>Operating Modes</b>	Return Loss, Power Meter, Light Source	
<b>Return Loss Meter</b>		
Nominal wavelengths <sup>1</sup>	1310, 1550 nm	1310, 1550, 1625 nm
Resolution	0.01 dB	
Measurement range	0 to 70 dB	
Measurement accuracy <sup>2</sup>	±0.7 dB (0 to 50 dB)	
	±0.9 dB (50 to 60 dB) <sup>3</sup>	
<b>Power Meter</b>		
Detector type	InGaAs	
Power measurement range	-85 to +15 dBm	
Max. permitted input level	+15 dBm	
Measurement accuracy <sup>4</sup>	±0.5 dB	
Overall measurement uncertainty <sup>5</sup>	±0.60 dB ±0.15 nW	
Automatic offset nulling	Yes	
Wavelength range/settings	1260 to 1650 nm, in 1 nm steps	
Calibrated wavelengths	1310, 1490, 1550, 1625 nm	
Display resolution	0.01 dB/0.001 µW	
Measurement units	dB, dBm, W	
Power meter functions	Abs, rel, pass/fail	
Auto functions <sup>6</sup>	Auto-λ	Auto single-wavelength detection
	Multi-λ	Auto multi-wavelength detection
Tone detection	270 Hz, 1 kHz, 2 kHz	
Warm up time	None, instant On	
<b>Light Source</b>		
Nominal wavelengths <sup>1</sup>	1310, 1550 nm	1310, 1550, 1625 nm
Spectral width	<5 nm	
Output power (settable in 0.01 dB steps)	-3 to -6 dBm	-6 to -9 dBm
Stability <sup>7</sup> 15 min/8 hr	0.02/0.2 dB	
Source modes	CW, tone, Auto-λ <sup>8</sup> , Multi-λ <sup>8</sup>	
Tone generator	270 Hz, 1 kHz, 2 kHz	
Optical interfaces	APC connector with interchangeable SC, FC, ST adapters	
<b>General</b>		
Laser Class	Class 1 Laser Product (IEC 60825-1:2007)	
Display	3.5-in color LCD touch screen, 4:3 ratio	
Data readout	Via USB interface	
Remote control capability	Via USB or Ethernet	
Inspection functions	Live, freeze, store end-face image, auto pass/fail	
Data storage	Up to 10,000 test results. Abs, rel. power with time stamp, inspection jpg	
Electrical interfaces	USB 2.0 (2 x host, type A, 1 x device, Micro-B)	
Power source	AC adaptor, 8x AA alkaline, or rechargeable LiON battery pack (option)	

VIAVI ORL-85

<b>General</b>		
Power mode	Active, Auto-Off (programmable)	
Battery life	>10 hr (LiON)/>8 hr (alkaline)	
Dimension (H x W x D) & Weight	ORL-85	208 x 112 x 64 mm (8.2 x 4.4 x 2.5 in) 750 g (1.6 lb)
	ORL-85P	208 x 153 x 64 mm (8.2 x 6.0 x 2.5 in) 850 g (1.85 lb)
Operating temp. range	-5 to +45°C (23 to 113°F)	
Storage temp. range	-25 to +55°C (-13 to 131°F)	

## Ordering Information

ORL-85 Optical Return Loss Meters include

- SmartClass Fiber instrument
- SC2 soft shoulder case
- Optical adapters: SC type (mounted) and FC type (interchangeable)
- Alkaline batteries (8x)
- Quick start manual and safety instructions

Description	Part Number
ORL-85 Return Loss Meter 1310, 1550 nm, APC	2311/21
ORL-85 Return Loss Meter 1310, 1550, 1625 nm, APC	2311/23
<b>Options and Accessories</b>	
P5000i digital analysis microscope with 4 tips	FBP-SD101
RBP2 Rechargeable Lilon battery pack 3.7 V/20 W	2305/90.02
PS4 power supply, 12 V, 2 A	2305/90.01
RBP2 Rechargeable Lilon battery pack with PS4 power supply	2305/90.04
SmartClass Fiber WiFi option including USB wifi-adaptor	2327/90.21
UC4 hands-free carrier	2128/01
SC2 soft shoulder case	2128/03
FC-type optical adapter	2155/00.05
LC-type optical adapter	2155/00.07
SC-type optical adapter	2155/00.26
ST-type optical adapter	2155/00.32
USB cable USB-A to Micro-USB	K807

1. ±20 nm

2. Under reference conditions 23°C ±3K, 45% to 75% rel. humidity, 9 µm test fiber with SC/APC ceramic connector, Normalization after a warm-up time of 20 minutes

3. Normalization with single-mode mandrel wrap that has >70 dB return loss

4. At calibrated wavelengths at reference conditions at -22 dBm (CW), 23°C ±3K, 9µm test fiber with SC/APC ceramic connector

5. At calibrated wavelengths from -85 dBm to +15 dBm, -5°C to +45°C. Overall measurement uncertainty for 1260 to 1650 nm: ±0.80 dB ±0.15 nW

6. With VIAVI optical light sources OLS-3x, OLS-5x, OLS-8x, OLTS-8x from 800 nm to 1625 nm: level > -60 dBm

7. Between -10 to +55°C with ΔT = ±0.3 K after a 20-minute warm-up

8. Works in conjunction with OLP-3x, OLP-55, OLP-85, OLTS-85, and ORL-85

## VIAVI Care Support Plans

Increase your productivity for up to 5 years with optional VIAVI Care Support Plans:

- Maximize your time with on-demand training, priority technical application support and rapid service.
- Maintain your equipment for peak performance at a low, predictable cost.

For more Information: go to [viasolutions.com/viavicareplan](https://viasolutions.com/viavicareplan)

### Features

\*5-year plans only

Plan	Objective	Technical Assistance	Factory Repair	Priority Service	Self-paced Training	5 Year Battery and Bag Coverage	Factory Calibration
 BronzeCare	Technician Efficiency	Premium	✓	✓	✓		
 SilverCare	Maintenance & Measurement Accuracy	Premium	✓	✓	✓	✓*	✓

© 2020 VIAVI Solutions Inc.  
Product specifications and descriptions in this document are subject to change without notice.  
smartclass-fiber-orl85-ds-fop-nse-ae  
30175934 903 0120