
Datasheet S0M-1

Reference Sine Oscillator Module for LIA-BV-150/LIA-MV-200 Series





Features	 Sine Wave Output from 5 Hz to 130 kHz Adjustable Frequency and Amplitude PLL for Synchronization to External Reference Plug-In Module for Series LIA-BV(D)-150/LIA-MV(D)-200 Lock-In Amplifiers 	
Applications	Reference Source for Lock-In Amplifier	
Block Diagram	SYNCHRONIZA- TION INPUT FREQUENCY CONTROL INPUT	Sine Wave Oscillator Amplitude Adjust OSCILLATOR OUTPUT Frequency Control Circuit Frequency Control Trimpot B801-1101-12
Specifications	Test Conditions	$Vs = \pm 5 V$, $Ta = 25^{\circ}C$
Oscillator Frequency	Frequency Range Manual Frequency Control Remote Frequency Control THD Temperature Coefficient	4 ranges, 5 Hz 130 kHz total (factory set at 1 kHz) 4 range settings via jumpers 5-6 and 7-8, adjustable frequency within range via 25-turn trimpot 4 range settings via digital control input pins 4 and 6, leave jumpers 5-6 and 7-8 open, adjustable frequency within range via control voltage 0 V + 10 V at pin 10 with reference to GND pin 8 0.8 % typ. 800 ppm/K allow 20 min warm-up time for good temperature stability
Oscillator Amplitude	Amplitude Range Amplitude Control Amplitude Accuracy	0 2 Vrms (factory set at 1 Vrms) 25-turn trimpot 100 ppm/K
Oscillator Output	Output Impedance Maximum Output Current	10 Ω (terminate with load > 1 k Ω) \pm 5 mA
External Synchronization	Synchronization Input Sync. Input Voltage Level Sync. Input Current	opto-coupler input with reference to synchronization ground pin 3 Low: - 0.8 V + 1.2 V, High: + 3.5 V + 6 V 0 mA @ 0 V, 6 mA @ + 5 V typ.
Power Supply	Supply Voltage Supply Current	\pm 5 V \pm 70 mA DE-SOM-1/R 14/SP/20.04.06/Page 1 of 2

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

F E T O

Datasheet SOM-1 Reference Sine Oscillator Module for LIA-BV-150/LIA-MV-200 Series 31 mm x 39 mm Board **Dimensions** Weight 10 g (0.022 lbs) Temperature Range Storage Temperature - 40 ... + 100 °C 0 ... + 60 °C Operating Temperature Absolute Maximum Ratings Power Supply Voltage $\pm 6 V$ 5 - 6 7 - 8 Jumper Settings (JP6) Frequency Range Frequency Range Selection 5 Hz ... 90 Hz close close 60 Hz ... 1.2 kHz close open 900 Hz ... 18 kHz close open open open 7 kHz ... 130 kHz Frequency Control Control Mode 1 - 2trimpot control open voltage control (external interface) close **External Synchronization** 3 - 4Synchronization open on off close **Jumper Positions Diagram** (\pm) Amplitude Adjust Frequency Adjust 2 mm pitch socket, 10-pin Connector Connector Type Oscillator Output Pin 2: oscillator output output GND Pin 8: Control Inputs Pin 4: frequency range control input, MSB frequency range control input, LSB Pin 6: frequency control input Pin 10: external synchronization input Pin 1: external synchronization input GND Pin 3: **Power Supply** Pin 9: power supply - 5V Pin 5: power supply + 5V power supply GND Pin 7: 0Î /F€ / V1 / HW / - A{ (/accessories / som-1.pdf Specifications are subject to change without notice. Information furnished herin is believed to be accurate and reliable. However, no responsibility is assumed by FEMTO Messtechnik GmbH for its use, nor for any infringement of patents or other rights granted by implication or otherwise under any patent rights of FEMTO Messtechnik GmbH. Product names mentioned may also be trademarks used here for identification purposes only.

© by FEMTO Messtechnik GmbH Printed in Germany

www.lasercomponents.com

Page 2

SOPHISTICATED TOOLS FOR SIGNAL RECOVERY

